




For installing: Pan-Ty, Dome-Top Barb Ty,
Sta-Strap, Contour-Ty, Super-Grip and In-Line Cable Ties of Subminiature,
Miniature, Intermediate and Standard cross sections.



ENGLISH

TOOL MAINTENANCE: GTS-E

This tool requires no maintenance.

REPLACEMENT KITS/ACCESSORIES:

(Sold Separately)

D: KGTS-ETL – Tension Locking Kit

E: KGTSBLD – Blade Replacement Kit

F: WB27359D01 – Blade Guard

WB25091A01 – Extended Blade Guard Kit

DEUTSCH

WARTUNG: GTS-E

Dieses Werkzeug ist wartungsfrei.

ERSATZTEILSATZ UND ZUBEHÖR:

(Separater Verkauf)

D: KGTS-ETL – Satz für Spannungssperre

E: KGTSBLD – Messersatz

F: WB27359D01 – Klingenschutz

WB25091A01 – Klingenschutz Satz (Ausgedehnt)

FRANÇAIS

ENTRETIEN DE L'OUTIL: GTS-E

Cet outil ne nécessite aucun entretien.

KITS DE REMPLACEMENT ET ACCESSOIRES:

(Vendu Séparément)

D: KGTS-ETL – Kit Raidisseur

E: KGTSBLD – Kit de Remplacement de Lame

F: WB27359D01 – Protege lame

WB25091A01 – Kit de Protege lame (Prolongé)

ITALIANO

MANUTENZIONE DELL'ATTREZZO: GTS-E

Questo strumento non richiede utenzaione.

KIT DI RICAMBIO E ACCESSORI:

(Venduti Separatamente)

D: KGTS-ETL – Kit di Blocco della Tensione

E: KGTSBLD – Kit per il Ricambio della Lama

F: WB27359D01 – Protezione della Lama

WB25091A01 – Kit di Protege lame (Esteso)

ESPAÑOL

MANTENIMIENTO DE LA HERRAMIENTA: GTS-E

Esta herramienta no requieren mantenimiento.

ACCESORIOS Y JUEGO DE REPUESTOS:

(Se vende separado)

D: KGTS-ETL – Juego de Fijación de la Tensión

E: KGTSBLD – Juego de Cuchilla de Repuesto

F: WB27359D01 – Protector de la Cuchilla

WB25091A01 – Juego de Protector de la Cuchilla (Extendido)

A 	— SUBMIN .070" (1.8mm)	— MIN .098" (2.5mm)	— INT .142" (3.6mm)	— STD .190" (4.8mm)
B 	0 – 1	1 – 3	3 – 5	5 – 8
C 				

日本語

工具のメンテナンス: GTS-E

本工具には、特別なメンテナンスは必要ありません。

交換部品キット/アクセサリ: (別売品)

D: KGTS-ETL – テンション設定ノブ固定キット

E: KGTSBLD – 交換用カッターキット

F: WB27359D01 – 交換用カッターガード

WB25091A01 – オプション品 ハイカット用カッターガード

お問い合わせ先: パンドUITコーポレーション日本支社

Tel: 03-6863-6060 Fax: 03-6863-6100

e-mail: jpn-toiwase@panduit.com

http://www.panduit.com

※Super-Grip スーパーグリップのテンション設定

A 	2.3mm幅 PLT80(B)	3.0mm幅 PLT100(B)	4.3mm幅 PLT150(B)	5.7mm幅 PLT200(B), PLT250(B) PLT300(B), PLT370S(B)
B 	1 – 3		3 – 5	5 – 8
C 				

Technical Support:
Email: techsupport@panduit.com
Tel: 1-800-777-3300

Technical Support: Panduit Europe
EMEA Service Center, Almelo, Netherlands
Tel: +31 546-580-452 • Fax: +31 546-580-441
EU Website: www.panduit.com/emea
EU E-mail: emeatoolservicecenter@panduit.com